



## Inprinta Capsule Filters

This main system filter is specifically designed for the requirement of digital inkjet printer filtration. The self contained unit is designed around an all-polypropylene construction with no binding agents, to give low extractables and ensure 100% compatibility with inkjet fluids. All capsule filters are available for standard solvent and UV ink systems.

- Capsule filters are pressure tested to guarantee capsule integrity.
- All filter housing is high grade Polypropylene.
- An integrated Vycon® core gives added security.
- Operating temperature from 0°C to 50°C (32°F to 122°F).
- 6bar (87psi) operating pressure.
- Optional filter materials.

### Features and Benefits

- High throughput.
- Multiple connectors.
- UV and solvent ink compatible.
- Large active filter area.
- Low pressure drop.
- Excellent particle retention.

### General Information

Inprinta capsules are self contained, ready to use, disposable devices. The filter body is constructed with natural or opaque black housing and available with a wide range of connector configurations to suit different systems. All capsules will provide consistent, reliable printing performance with maximised print head protection.

### Filtration Technology


The filters are manufactured using a range of different materials and design characteristics. Our Polyfil™ and Klearfil™ pleated polymeric membranes are engineered as the principal barrier to any foreign bodies or aggregates. Our Polyfil™ media benefits from a high pleat construction and a large surface area which offers a high flow rate and a minimal pressure drop, with focused spectrum particle removal properties. Our Klearfil™ media has 8 graded filtration layers allowing for wide spectrum particle removal, gel retention and a high dirt holding capacity. The deep filter pack also demonstrates minimum distortion under pressure and a long service life.

An integrated secondary level of protection is added through an innovative design and the utilization of BioVycon™ as a central column filter. BioVycon™, a co-sintered solid-state separation material, is manufactured from an ultra-pure, highly modified polymeric material with the lowest levels of particulates and extractables.


### Strength and Durability

The filter housing is manufactured to take the stresses of inkjet. The polypropylene materials are resistant to all standard solvents, and the wall strength, design and construction will provide a long service life.

Liquid Flow Rates versus Differential Pressure for Polyfil™ Capsule



Liquid Flow Rates versus Differential Pressure for Klearfil™ Capsule



### Connectors


For the many inkjet systems in the market, we provide a wide range of connectors allowing for quick, simple and clean changeovers. Jaco®, CPC, luer and barb connectors are all available in a variety of configurations. Connectors are also available with elbows, for situations where space is at a premium.

Connector	Inlet/Outlet Styles
A	1/4" to 3/8" barb
B	3/8" to 1/2"
C	1/2"
D	1/4" NPT (male)
E	3/8" NPT (female)
F	CPC
G	Jaco® 40-6mm-6 90° (elbow) 6mm tube
H	Jaco® 10-2mm-2 male connection 6mm tube
J	Jaco® 10-6mm-2 male connection 6mm tube
K	Jaco® 40-6mm-6 90° (elbow) 6mm tube with fitted last chance filter
L	Male connection for 4mm tube
N	90° (elbow) 1/4" to 3/8" barb
P	Luer
Q	90° (elbow) Luer

## Filter Efficiency

- Capsule filters have removal efficiencies from 0.5µm to 60µm
- All filters validated to OSU-F2 Single pass test to Beta 5000 (99.98% efficiency)
- Manufactured for high service life

## Filter Media






## Testing

- Filter cycles:** Tested to 180,000 cycles/pulses at 80psi.
- Pressure validation:** 100% of capsule filters tested to 6 bar.
- Filter integrity:** Filter units are bubble tested for verified optimum micron rating.

## Technical Information

<b>Filter media</b>	Polypropylene, PES, nylon, PTFE and glass fibre
<b>Housing material</b>	Polypropylene
<b>Housing colour</b>	Opaque black and natural
<b>Micron rating</b>	0.5µm, 1µm, 3µm, 5µm, 10µm, 20µm, 40µm and 60µm (absolute) (additional ratings are available on request)
<b>Filter dimensions</b>	Microcap™ 70mm x 52mm (plus connectors) Microprint™ 70mm x 46mm (plus connectors) Microjet™ 100mm x 27mm (plus connectors)
<b>Filter area</b>	Microcap™ 500cm² (77.5in²) Microprint™ 500cm² (77.5in²) Microjet™ ???cm² (??in²)
<b>Maximum operating pressure</b>	6bar (87psi)
<b>Operating temperature</b>	From 0°C to 50°C (32°F to 122°F)



## Ordering Information

### Microcap™ (Fully Moulded)

8089 - 

#### Micron Ratings

0050	0.5µm
0100	1µm
0300	3µm
0500	5µm
1000	10µm
2000	20µm
4000	40µm
6000	60µm

#### Filter Media

1	Polyfil™
5	Klearfil™

#### Housings

N	Natural
C	Opaque black

#### Connectors

AA	¼" barb
DD	¼" NPT (male)
FF	CPC
GG1	¼" Jaco® 90°
GG2	6mm Jaco® 90°
JJ1	¼" Jaco®
JJ2	6mm Jaco®
PP	Luer
QQ	Luer 90°



### Microprint™

8096 - 

#### Micron Ratings

0050	0.5µm
0100	1µm
0300	3µm
0500	5µm
1000	10µm
2000	20µm
4000	40µm
6000	60µm

#### Filter Media

1	Polyfil™
5	Klearfil™

#### Housings

N	Natural
C	Opaque black

#### Connectors

FF	CPC
JJ1	¼" Jaco®
JJ2	6mm Jaco®



### Microjet™

8131 -  - 1 - PP - 

#### Micron Ratings

0500	5µm
1000	10µm

#### Housings

N	Natural
C	Opaque black



## Contact us

For further information on our product range or manufacturing services, please contact Inprinta on the details below:

### Inprinta

Queensway, Stem Lane  
New Milton, Hampshire  
BH25 5NN, UK

T +44 (0)1425 612010  
E [info@inprinta.com](mailto:info@inprinta.com)

301 Business Lane  
Ashland, Virginia 23005, USA

T +1 804 550 1600  
E [info@inprinta.com](mailto:info@inprinta.com)

Chengdong Area  
Square Industrial Park, North District  
Xiaonan Economic Development Zone  
Xiaogan, 432000, China

T +86 (0)712 2878955  
E [info@inprinta.com](mailto:info@inprinta.com)

[www.inprinta.com](http://www.inprinta.com)

Inprinta and Vyon are registered trademarks of Porvair Plc.

BioVyon, Klearfil, Microcap, Microjet, Microprint and Polyfil are trademarks of Porvair Plc.

Jaco is a registered trademark of Jaco Manufacturing Company.

© Copyright 2010. Inprinta. All rights reserved.

Whilst every effort has been made to ensure the accuracy of this document, due to continuous product development, the data contained is subject to constant revision and Inprinta reserves the right to change, alter or modify its contents.

Inprinta products are not the original, but are compatible parts and they are not produced by, or have been endorsed by the manufacturers specified. Inprinta is not associated with, nor represents any of the companies stated in Inprinta marketing material and literature. All other companies referenced herein are trademarks and/or registered trademarks of their respective companies.

## Inkjet Capsule Filters

